



Hospital-Grade Tamper-Resistant Weather-Resistant 15A Self-Test Duplex GFCI

Features & Benefits

Hospital Grade GFCI self-test CH versions feature a factory broken split circuit tab allowing you to control half of the receptacle.

Specifications

General Info

| | | | |
|-------------------|--|-----------------------|--------|
| Product Line | Pass & Seymour | Color | Red |
| Country Of Origin | China | Number of Receptacles | 2 |
| Outlet Type | Commercial, GFCI, Outdoor, Tamper-Resistant, Weather-Resistant | Type | Outlet |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.73 in | Product Depth US | 1.13 in |
| Product Height US | 4.2 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|---------------------|-------------|----------------|---------|
| Is Tamper-Resistant | Yes | Amperage | 20 A |
| Number of Poles | Double Pole | Indoor/Outdoor | Outdoor |
| Voltage | 125.0 V | | |