



GFCI receptacles from the radiant® Collection self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. Meeting National Electrical Code requirements for ground fault protection, GFCI receptacles make it easier to recognize and fix trips right where they happen – no more confusion at the breaker box. 20A outlets are ideal for use with larger appliances and in commercial settings, as well as to meet regional requirements (Chicago, Canada). GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Spec-Grade devices are engineered to meet federal specifications for use in commercial installations.

## Features & Benefits

Alarm rated at 60 db at 10 feet

Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the trip indicator light (red LED) flashes to signal that the GFCI should be replaced

Feed-thru wiring configuration allows GFCI to protect downstream receptacles

Mounting screws are shipped captive in the device and wall plate for easier installation

Thinner than competitors' GFCI Receptacles: leaves more room for wires in the box

One-piece, brass, triple-wipe power contacts for lasting retention

Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected

Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly

Dual-direction test and reset button colors match the device face

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Features	Audible Alarm
Outlet Type	Commercial, GFCI, Indoor, Self-Test, Tamper-Resistant	Application Sector	Residential/Commercial
Standard	cULus, UL Listed, FSUL	Warranty Type	1-Year Limited Warranty
Type	Outlet		

---

## Dimensions

---

Product Width US	1.73 in	Product Depth US	1.03 in
------------------	---------	------------------	---------

---

Product Height US	4.2 in
-------------------	--------

---

## Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

## Additional Information

---

Product Environmental Profile	Yes
-------------------------------	-----

---

## Technical Information

---

Is Tamper-Resistant	Yes	Interrupt Rating	4 A
---------------------	-----	------------------	-----

---

Frequency Rating	60 Hz	Trip Range	5±1 mA
------------------	-------	------------	--------

---

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

---

Indoor/Outdoor	Indoor	Voltage	125.0 V
----------------	--------	---------	---------

---