



Pass and Seymour  
Watertight NEMA 4X/6P Locking Connector, Yellow  
Part No. 25W47



Locking Watertight Connector, 15amp 125volt, NEMA Configuration L5-15, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, and IP67 rated.

## Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather.

Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

Color coded sealing bushings provided for large range of cord diameters

Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.

Devices resist high-pressure hose down of 1,500 psi.

Large ribs on body for a superior grip when mating.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 498		

### Dimensions

Product Width US	1.85 in	Product Length US	4.03 in
------------------	---------	-------------------	---------

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	701645
------------	-----	-----------------	--------

### Technical Information

Number of Wires	3	Amperage	15 A
-----------------	---	----------	------

---

---

Number of Poles

Double Pole

Wire Size

18 - 10 AWG

---

Voltage

125.0 V

---