



Pass and Seymour
Phenolic Medium Base Lampholder 4-Terminal 250V, White
Part No. 276WH



Medium base, phenolic, one-piece keyless, 4 terminals with Tamper-Resistant-drive screws, fits 3 1/4-inch and 4-inch boxes, with cage neck.

Features & Benefits

Quality Materials.

Durability.

Time-tested design. :

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|------------------------|
| Product Line | Pass & Seymour | Color | White |
| Country Of Origin | China | Application Sector | Residential/Commercial |
| Standard | UL listed | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|------|--------------|-----|
| cULus ListingNumber | 1204 | cULus Listed | Yes |
|---------------------|------|--------------|-----|

Technical Information

| | | | |
|------------------|---------|---------|---------|
| Frequency Rating | 660Watt | Voltage | 250.0 V |
|------------------|---------|---------|---------|