



Pass and Seymour  
50A 250V 6-50R Straight Blade Single Flush Receptacle, 2-Pole, 3-Wire  
Part No. 3804



Straight Blade Receptacle 2-Pole 3-Wire 50A 250V

## Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	China
Standard	UL 498		

### Dimensions

Product Width US	2.5 in	Product Depth US	2.2 in
Product Height US	3.75 in		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	140596
cULus Listed	Yes	CSA File Number	16063

### Technical Information

Connection	Wire Ground	Number of Wires	3
------------	-------------	-----------------	---

---

Amperage	50 A	Number of Poles	Double Pole
Wire Size	4	Voltage	250.0 V

---