



Straight Blade Receptacle 30A 125/250V

## Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	China
Standard	UL 498		

### Dimensions

Product Width US	2.5 in	Product Depth US	1.9 in
Product Height US	3.75 in		

### Technical Information

Connection	Non Ground	Number of Wires	3
Amperage	30 A	Number of Poles	3-Way
Wire Size	4	Voltage	125.0 V