

Single Receptacle 2-Pole 3-Wire 20A 277V Grounding



## Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Receptacle Type	Single
Number of Receptacles	1	Application Sector	Residential/Commercial
Standard	UL20/498		

### Dimensions

Product Width US	1.437 in	Product Depth US	0.866 in
Product Height US	1.74 in		

### Technical Information

Is Tamper-Resistant	No	Number of Wires	3
---------------------	----	-----------------	---

---

Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 12 AWG	Is Weather Resistant	No
NEMA Configuration Code	7	Voltage	277.0 V

---