



NEMA 1 Nylon Enclosure with 1/2 inch and 3/4 inch Knockouts

Features & Benefits

High horsepower rating of 20HP. Compact design. Gull-wing shaped brass terminal pressure clamps. Constructed of glass-reinforced thermoplastic. Two-point contact arms. One-piece contact carrier. UL508 and cULus Listing of individual device and assembled device within enclosure. Heavy-duty zinc-plated steel strap. Two brass rivets secure strap to housing. External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals. Oversized silver alloy contacts. 2-3/4 inch hubs (7812-EX and 7813-EX). 2-1/2 inch knockouts on back and 2-1/2 inch -3/4 inch knockouts on top and bottom (7812-P, 7813-P, 7806-P). 2-1/2 inch knockouts on bottom and back (7832 and 7833).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Standard	UL Listed

Dimensions

Product Width US	2.825 in	Product Height US	3.91 in
------------------	----------	-------------------	---------

Technical Information

Amperage	30 A	Wattage	1 W
Voltage	600.0 V		