




Cablofil
CabloPort Block with FASP 6" Long [943529]
Part No. 943529



Cablo-Port is a UV and Weather resistant rubber base that creates a cushion between rooftop mounted equipment and sensitive roofing materials. Available in two styles, the Standard style is perfect for smaller loads and tight spaces and the Widebody design provides a broad base to minimize roof pressure and a larger area for glue application. Cablo-Port is also available with a wide variety of pre-mounted support options, including FAS P and Channel.

Features & Benefits

Flat roof support: For support of tray, piping or other items on flat roofs.

Two support styles: FAS Profile for wire mesh trays or 13/16' galvanized channel (14 ga.) for ladder tray, piping or other material support.

Install: on any roofing material or other flat surface.

Supports are available in: one standard finish and two optional finishes.

Curb style maximum load: 750 lbs. (CPP5 and CPS5 - maximum load 200 lbs.).

Two rubber base designs: Standard Curb and Widebody style

Widebody design: has 1,000 lbs/ft maximum load and provides 5 times the surface area to minimize roof material pressure, increase load capacity and provide over 120 square in/ft for glue application.

Specifications

General Info

Product Line	Cablofil	Finish	Other
UPC Number	800388019140	Country Of Origin	United States
Application Sector	Commercial	Type	Fasteners

Dimensions

Product Width US	6.0 in	Product Weight US	3.0 lb
Product Volume US	0.104 cu ft	Product Depth US	6.0 in
Product Height US	5.0 in		

Buy American Act Compliance

BAA	Yes
-----	-----
