




Cablofil
CPORT Strut Bridge 60" Sup [943646]
 Part No. 943646



Cablo-Port is a UV and Weather resistant rubber base that creates a cushion between rooftop mounted equipment and sensitive roofing materials. Available in two styles, the Standard style is perfect for smaller loads and tight spaces and the Widebody design provides a broad base to minimize roof pressure and a larger area for glue application. Cablo-Port is also available with a wide variety of pre-mounted support options, including FAS P and Channel.

Features & Benefits

Non Penetrating Weather Resistant Bases: 100% recycled bases won't deteriorate over time. UV resistant rubber supports 1000lb/ft. Composite material accepts screws or other mechanical fasteners. Choice of two base styles -- standard or widebody.

Wide Variety of Support Options: Height adjustability bridges rooftop gaps, structures, or other utility pathways. Angled to adapt to any roof pitch. Multiple level for stacking cable pathways.

Improves Safety: Reflective safety strip keeps cable pathways visible on dark roofs and in low light conditions.

Fast Shipment: Most assemblies ship in 1-3 days ARO.

Pre-installed Supports: Multiple support options designed to speed installation. Slotted Channel supports ladder tray, wire mesh tray and tubing. Metal supports available in 3 finishes: Pre-galvanized (PG, Standard), Hot-Dipped Galvanized (GC, Optional), and 304L Stainless Steel (S4, Optional).

Extends Life of Roof: Rubber base cushions heavy metal supports. Standard or Widebody styles reduce pressure points on sensitive roofing materials. Dampens vibrations.

Green Buildings: 100% recycled rubber construction assists with building qualification for LEED credits.

Specifications

General Info

Product Line	Cablofil	Finish	Other
UPC Number	800388020313	Country Of Origin	Canada

Dimensions

Product Width US	6.0 in	Product Weight US	26.988 lb
Product Volume US	1.167 cu ft	Product Depth US	60.0 in
Product Height US	5.6 in		

Buy American Act Compliance

BAA	Yes
-----	-----
