



Perfect anywhere you'd like to turn lights on and off with the simplest touch, while also enjoying the ability to dim. Featuring a translucent glass-like face, this modern dimmer lets you control your lights by simply pressing a finger to the center circle to turn lights on/off, or use the + or - on the side to dim. Use the dimmer switch on its own to control a 0-10V light or fixture from a single location, or pair with a 3-way switch to control a single light source from two locations. Pair with the matching Touch Switch for a consistent control-style throughout a room, or your entire house.

This dimmer* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

* Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Usable in both single-pole and 3-way applications.

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

For use with dimmable 0-10V bulbs or fixtures. Features intuitive touch control for switching on/off and adjusting light levels.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	White	Country Of Origin	China
Features	Antimicrobial Protection, Indicator Lights	Switch Type	Touch

Number of Switches	1	Standard	cULus
--------------------	---	----------	-------

Warranty Type	Limited Lifetime Warranty
---------------	---------------------------

Dimensions

Product Width US	1.77 in	Product Depth US	1.62 in
------------------	---------	------------------	---------

Product Height US	1.77 in
-------------------	---------

Technical Information

Electrical Rating	120V 10A (0-10V Fluorescent), 120V 10A (0-10V LED)	Connection	Screw Terminals
-------------------	--	------------	-----------------

Number of Gangs	1	Bulb Compatibility	Fluorescent, LED
-----------------	---	--------------------	------------------

Number of Poles	3-Way, Single Pole	Wattage	700 W
-----------------	--------------------	---------	-------

Mounting Type	Box	Voltage	0 to 10 V
---------------	-----	---------	-----------

Connection Type	Internal Pressure Plates	Load	LED, Fluorescent
-----------------	--------------------------	------	------------------
