




adorne Collection  
adorne® 20A Paddle Switch, Magnesium, with Microban®  
Part No. ASPD2032M4



A sleek update to the standard toggle, this modern light switch lets you turn lights on and off with ease and style. Use this 20A light switch on its own to control a light or fixture from a single location, or pair with a second switch for 3-way control.

This switch\* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

\* Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

## Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Usable in both single-pole and 3-way applications.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	Magnesium	Country Of Origin	China
Features	Antimicrobial Protection	Switch Type	Paddle
Number of Switches	1	Standard	cULus
Warranty Type	Limited Lifetime Warranty		

---

## Dimensions

---

Product Width US	1.77 in	Product Depth US	1.59 in
------------------	---------	------------------	---------

---

Product Height US	1.77 in
-------------------	---------

---

## Technical Information

---

Connection	Screw Terminals	Number of Gangs	1
------------	-----------------	-----------------	---

---

Amperage	20 A	Number of Poles	3-Way, Single Pole
----------	------	-----------------	--------------------

---

Mounting Type	Box	Voltage	120.0 V
---------------	-----	---------	---------

---

Connection Type	Internal Pressure Plates
-----------------	--------------------------

---