



Pass and Seymour  
Strain Relief Grips  
Part No. BOX120

Wide range, Straight male, Dust tight grips. 1 1/2-inch NPT, 1.200-1.500-inch.



## Features & Benefits

Wide range grips are recommended for use in wiring of enclosures, power boxes, machine tools, and Includes insulated power centers. bushing.

1400 lbs breaking strength rating (in US lbs)

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Support and Strain Relief Grips, Various Types of Pulling	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)	Type	Dust Tight

### Dimensions

Product Width US	1.5 in	Product Length US	1.5 in
------------------	--------	-------------------	--------

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	67507
------------	-----	-----------------	-------

### Technical Information

Maximum Cable Range	1.2 in	Minimum Cable Range	1.5 in
---------------------	--------	---------------------	--------

---

Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
Load	Strain Relief Grips are designed to prevent tension from being transferred to junctions and terminals on electrical cord, cable and conduit, therefore providing a more secure electrical structure.		

---