



Wide range, Straight male, Dust tight grips. 1 1/4-inch NPT, 0.940-1.250-inch.

## Features & Benefits

Wide range grips are recommended for use in wiring of enclosures, power boxes, machine tools, and power centers.

Includes insulated bushing.

700 lbs breaking strength rating (in US lbs)

## Specifications

### General Info

|              |   |                    |            |
|--------------|---|--------------------|------------|
| Product Line | Pass & Seymour  | Country Of Origin  | Mexico     |
| Construction | Support and Strain Relief Grips, Various Types of Pulling | Application Sector | Industrial |
| Standard     | UL/CSA Approval (consult factory)                         | Type               | Dust Tight |

### Dimensions

|                  |         |                   |         |
|------------------|---------|-------------------|---------|
| Product Width US | 1.25 in | Product Length US | 1.25 in |
|------------------|---------|-------------------|---------|

### Listing Agencies / 3rd Party Agencies

|            |     |                 |       |
|------------|-----|-----------------|-------|
| CSA Listed | Yes | CSA File Number | 67507 |
|------------|-----|-----------------|-------|

### Technical Information

|                     |  |                     |  |
|---------------------|--|---------------------|--|
| Maximum Cable Range | 0.94 in  | Minimum Cable Range | 1.25 in  |
| Capacity            | Various Cable Diameter Ranges  | Mounting            | Consult the Factory for Mounting Recommendations |
| Load                | Strain Relief Grips are designed to prevent tension from being transferred to junctions and terminals on electrical cord, cable and conduit, therefore providing a more secure electrical structure. |                     |  |