



**On-Q**  
**In Wall TV Power Kit with USB White**  
Part No. CPU306WV1



Easily hide power and AV cables inside the wall without modifying electrical wiring. This pre-wired kit includes everything needed to extend power for a wall mounted TV while providing the ultimate flexibility with the innovative decorator based power inlet strap and the recessed box with Dual USB Type A receptacle. Kit includes a Dual USB-A Tamper Resistant Outlet to power compatible streaming devices.

## Features & Benefits

High-speed Cat 5e termination point for digital data services

Compatible with all TV power plugs, USB type A connections even right angle cords

Hook up a digital TV adapter, cable box, sound bar, or streaming media devices such as Apple TV™ or Roku™

Unique brush strap cable catcher prevents cables from falling behind the wall

Unique decorator based power inlet strap provides flexible project support for ganging other AV connections

## Specifications

### General Info

Product Line	On-Q	Replaced by Part Number	
Color	White	Finish	Matte
UPC Number	804428434658	Country Of Origin	China
Included	Cutting template, Mounting Hardware	Outlet Type	Indoor, Residential, Tamper-Resistant
Application Sector	Residential	Warranty Type	1 Year from Day of Sale
Type	Tamper-Resistant		

### Listing Agencies / 3rd Party Agencies

ETL Listed Yes

---

## Technical Information

---

Connection	(2) USB Type A, (1) Cable Access, (2) Outlets	Amperage	15 A
Input Voltage	125 V	Indoor/Outdoor	Indoor
Mounting Type	Wall	Operating Temperature	32°-122°F

---