



**On-Q**  
**17-inch Dual-Purpose In-Wall Enclosure**  
Part No. ENP1700NA



The 17-inch Dual-Purpose In-Wall Enclosure is engineered to provide storage of structured wiring and AV components. The ENP1700NA is constructed of Wi-Fi transparent material to manage wireless components and AV devices at point-of-use locations, like directly behind a TV or other media centers. It can also be used for structured wiring purposes, such as networking equipment, access points, switches and more. The ENP1700NA is compatible with devices like the Samsung One Connect Box, Apple TV, Roku, Amazon Fire TV, network switches, 3rd party structured wiring components and more. Includes a split cover, trim ring and drywall clips, allowing for both new construction and retrofit installations.

## Features & Benefits

Designed for in-wall storage and distribution of structured wiring and AV components

Can be placed behind most TV wall-mounts including SANUS premium TV mounts

Compatible with devices like the Samsung One Connect Box, Apple TV, Roku, Amazon Fire TV, 3rd party structured wiring components and more

Trim ring conceals drywall cut out for clean finish and smooth transition to wall surface

Split cover is low profile and designed to snap into place. Split design supports removal and access to components even if partially covered

Knockout configurations support conduit and in-wall wired connections, while a cable pass through on cover allows for outside cable connections

Features (2) AC knockouts to accommodate a single gang junction box to power devices in enclosure

Universal mounting grid maximizes compatibility with 3rd party devices without additional mounting brackets

Features drywall clips to allow both retrofit and new construction installations

UL Listed and constructed of Wi-Fi transparent ABS plastic to ensure uninterrupted performance of wireless devices

Proudly made in the USA

## Specifications

### General Info

Product Line	On-Q	Replaced by Part Number	
Color	White	UPC Number	804428434146
Country Of Origin	United States	Package Quantity	1
Application Sector	Residential/Commercial	Standard	RoHS, UL, cULus
Type	Enclosure		

---

## Dimensions

---

Product Width US	14.37 in	Product Depth US	3.88 in
------------------	----------	------------------	---------

---

Product Height US	17.02 in
-------------------	----------

---

## Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

## Additional Information

---

RoHS Conformant	Yes
-----------------	-----

---

## Technical Information

---

Compatibility	Paintable with Rust-Oleum paint for plastic or equivalent	Thickness	0.1 in
---------------	---	-----------	--------

---

Enclosure Type	Dual Purpose	Frame	Injection-molded plastic
----------------	--------------	-------	--------------------------

---

Operating Temperature	32°-122°F	Mounting	Consult the Factory for Mounting Recommendations
-----------------------	-----------	----------	--

---

Environmental Conditions	0 to 93% (relative humidity, non-condensing)
--------------------------	--

---