



Ortronics

1000Base T RJ45, Copper No Wave Length, 100 meters, DOM, Commercial Temperature 100% Fortinet compatible.

Part No. FG-TRAN-GC-L



1000BASE-T SFP Copper RJ45 100m Transceiver, Copper, 100m, RJ-45, Non-DDM, C-Temp

Features & Benefits

Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.

Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page.

Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.

99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.

98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.

Specifications

General Info

Product Line	Ortronics	UPC Number	662875079682
Country Of Origin	China	Warranty Type	Lifetime
Type	Transceiver		

Technical Information

Fiber Optic Cable Type	Passive Twinax
------------------------	----------------