



The FSP-201 mounts in an outdoor lighting fixture and provides multi-level control based on motion and/or daylight contribution. It controls 0-10 VDC dim-to-off LED drivers or ballasts, or works with a power pack to control other loads. When used with an FSP-Lx Lens, the sensor is rated for wet and cold locations. All control parameters are adjustable via a wireless configuration tool capable of storing and transmitting sensor profiles.

## Features & Benefits

Fully adjustable high and low dimmed light levels; optional dusk to dawn control	Controls 0-10V dim-to-off LED drivers or ballasts, or works with a power pack to control other loads
Hold off setpoint with automatic calibration option for convenience and added energy savings	Adjustable via handheld wireless configuration tool
IP66 rated with choice of lenses for wet and outdoor locations, and mounting heights from 8' to 40'	Adjustable time delay and cut off delay

## Specifications

### General Info

Product Line	Wattstopper	UPC Number	754182931231
Country Of Origin	China		

### Dimensions

Product Width US	1.0 in	Product Weight US	0.17 lb
Product Volume US	13.32 cu in	Product Depth US	2.0 in
Product Height US	3.7 in		

### Additional Information

RoHS Conformant	Yes	Security	Yes
Product Environmental Profile	Yes		

### Technical Information

---

Sensor Type

Daylight, Occupancy

---