




radiant Collection
radiant® Multi-Location Remote Dimmer, White
Part No. HMRWCCV4



Provides precise dimming control of a light or fixture from another part of the room through this second on-wall controller. Must be used with the Multi-Location Master Dimmer. Part of the radiant® Collection, it also features clean lines and smooth control for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Installs easily with 3-way wiring for multi-location dimming. For use with most Incandescent, CFL/LED (with the exception of 0 - 10v options) and MLV dimmable bulbs.

Constant memory features returns lights to their previous level after a power failure or outage.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

No derating required in multi-gang applications.

More color options available. (For Tri-Color version: Includes three interchangeable face plates in white, light almond, and ivory for flexible customization.)

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	White	Country Of Origin	China
Features	Indicator Lights	Switch Type	Paddle
Number of Switches	1	Warranty Type	Limited Lifetime Warranty

Dimensions

Product Width US	1.75 in	Product Depth US	1.25 in
------------------	---------	------------------	---------

Product Height US 4.25 in

Technical Information

Number of Gangs 1 Amperage 15 A

Bulb Compatibility CFL, Incandescent, LED Number of Poles 3-Way, Multi-Location, Single Pole

Wattage 700 W Mounting Type Box

Voltage 120.0 V
