



The Flexible Pass-Through Grommet is an in-wall cable management solution meant for speed!

The flexible Pass-Through grommets hide low voltage cables in the wall and out of sight. Utilizing a 1.5-inch hole saw (not included), cut an opening in the ceiling or wall, run cabling and secure the mini Pass-Through grommets in under 20 min. The flexible grommet has directional ribs that create a secure friction fit with the drywall opening to prevent slippage or fall out. It supports up to four low voltage cables and is ideal for HDMI, TV cabling, IP Cameras, wireless access points, and wall-mounted speakers,

## Features & Benefits

Hide low voltage cables in the wall and out of sight

Installs in under 20 minutes

Secures to wall or ceiling with friction and ribbed design

Requires a 1.5 in. Hole Saw (not included) and supports up to 4 low voltage cables in a small footprint

Ideal for HDMI and TV Cables, IP Cameras, Wireless access points, and wall mounted speakers.

Contents include: 10 Flexible Pass-Through Grommets and Instruction sheet.

## Specifications

### General Info

Product Line	On-Q	Replaced by Part Number	
Color	White	Finish	Matte
Country Of Origin	China	Construction	Rubber
Installation Location	In-Wall	Application Sector	Residential/Commercial
Warranty Type	Manufacturer's Limited Warranty	Type	Grommet

### Dimensions

Product Width US	2.27 in	Product Weight US	0.025 lb
Product Depth US	2.27 in	Product Height US	1.35 in
Product Length US	2.27 in		

---

## Technical Information

---

Cable Entry	1-1/2 in	Number of Holes	1
-------------	----------	-----------------	---

---

Environmental Conditions	Not intended for fire-rated walls
--------------------------	-----------------------------------

---