



On-Q
In-Wall TV Connection Kit Black
Part No. HT2102BKVI



The In-Wall TV Connection Kit provides recessed power and cable management for a wall mounted TV. This kit manages excess cabling via in-wall storage and recessed outlet to allow TVs to mount flush to wall. Compatible with all TV Power plugs, even right angle cords. The outlet accomodates power for multiple devices like cable box, soundbar, or streaming player like Roku or Apple TV. Kit includes recessed wall plate with integrated LV brush opening, junction box, 15A tamper resistant outlet and wall plate.

Features & Benefits

Manages excess cable via in-wall storage, while providing slack for: convenient access to back of TV when needed

Unique brush strap cable catcher prevents cables from falling behind the wall

All contents are Black in color to blend seamlessly with TV and Wall Mount Brackets

Compatible with all TV power plugs, even right angle cords and wall warts

Kit includes: Recessed wall plate with integrated LV brush opening, junction box, 15A tamper resistant outlet and wall plate

Specifications

General Info

Product Line	On-Q	Color	Black
Finish	Matte	UPC Number	804428433729
Country Of Origin	China	Receptacle Type	5-15R
Application Sector	Residential	Standard	Kit Includes UL Approved Components

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Wire Gauge	14 AWG	Cutout	1 Cable Access, 1 Outlet
------------	--------	--------	--------------------------

Amperage	15 A	Indoor/Outdoor	Indoor
Orientation	Vertical	Number of Outlets	2
Voltage	125.0 V		
