



Receptacle Single 3-Wire 20A 277V Turnlok®

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Application Sector	Industrial	Standard	UL 498

Dimensions

Product Width US	1.61 in	Product Depth US	1.19 in
Product Height US	2.29 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile Yes

Technical Information

Number of Wires	3	Amperage	20 A
-----------------	---	----------	------

Number of Poles	Double Pole	Wire Size	4 AWG
-----------------	-------------	-----------	-------

Voltage	277.0 V
---------	---------
