



Decorator Slide De-Hummer Control, 4-Speed, 1.6A

Features & Benefits

Tough impact-resistant thermoplastic housing.

Superior heat management: no time wasting break off tabs.

Can be used with patented Snap-In Light Module (sold separately).

Power-failure memory.

Device comes with wired leads.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	China	Application Sector	Residential
Standard	UL Listed	Type	Dimmer

Dimensions

Product Width US	1.74 in	Product Depth US	1.28 in
Product Height US	4.185 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Operating Cycles	100000	Amperage	1.6 A
------------------	--------	----------	-------

Number of Poles

Single Pole
