

Decorator Slide Fan Control, Preset/3-Speed/5A



Features & Benefits

Tough impact-resistant thermoplastic housing.

Power-failure memory.

Superior heat management: no time wasting break off tabs.

Exclusive screw-pressure-plate back wire terminals eliminates wire nuts.

Can be used with patented Snap-In Light Module (sold separately).

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|-------------|
| Product Line | Pass & Seymour | Color | White |
| Country Of Origin | China | Application Sector | Residential |
| Standard | UL Listed | Type | Dimmer |

Dimensions

| | | | |
|-------------------|----------|------------------|---------|
| Product Width US | 1.74 in | Product Depth US | 1.28 in |
| Product Height US | 4.185 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|------------------|-------------|----------|---------|
| Operating Cycles | 100000 | Amperage | 5 A |
| Number of Poles | Single Pole | Voltage | 120.0 V |
