

Infinium M4 pre-terminated cassettes with method B provide rapid deployment and have a flipped polarity inside the modules, which use key-up to key-up MPO adapters and allows for straight through patching. The rugged metal housing offers additional durability and includes a built-in internal bend limiting feature to assure optimum optical performance.



Features & Benefits

| | |
|---|--|
| Fully Compatible with Infinium INFC Enclosures | 4 Cassettes Fit into 1U |
| Front Adapter Housing Colors Follow TIA/EIA-568.3-D Suggested Color Identification Scheme | Each cassette has a data label with insertion loss value for each port |

Specifications

General Info

| | | | |
|-------------------|---------------|--------------------|--------------|
| Product Line | Ortronics | UPC Number | 662875001263 |
| Country Of Origin | United States | Application Sector | Commercial |
| Standard | TIA-568-C.3 | Type | Cassette |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 3.45 in | Product Depth US | 4.77 in |
| Product Height US | 1.14 in | | |

Additional Information

| | |
|-----------------|-----|
| RoHS Conformant | Yes |
|-----------------|-----|