



Pass and Seymour
Light Duty, Standard Length, Flexible Eye
Part No. PL2502

Light Duty, Standard Length, Flexible Eye. Cable Diameter - 2.500-2.990-inch, Mesh Length - 28-inch, Break Strength - 13,000 lbs.



Features & Benefits

Light-Duty grips are the most economical pulling grips for many applications, such as industrial plant wiring, and rewiring, and underground electrical pulls.

Mesh Length: 28

Specifications

General Info

| | | | |
|--------------|---|--------------------|------------|
| Product Line | Pass & Seymour | Country Of Origin | Mexico |
| Construction | Support and Strain Relief Grips, Various Types of Pulling | Application Sector | Industrial |
| Standard | UL/CSA Approval (consult factory) | | |

Technical Information

| | | | |
|---------------------|-------------------------------|---------------------|--|
| Maximum Cable Range | 2.5 in | Minimum Cable Range | 2.99 in |
| Capacity | Various Cable Diameter Ranges | Mounting | Consult the Factory for Mounting Recommendations |
| Load | Approx. Break Strength: 13000 | | |