

Light Duty, Standard Length, Flexible Eye. Cable Diameter - 3.000-3.490-inch, Mesh Length - 30-inch, Break Strength - 16,200 lbs.



Features & Benefits

Light-Duty grips are the most economical pulling grips for many applications, such as industrial plant wiring, and rewiring, and underground electrical pulls.

Mesh Length: 30

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
--------------	----------------	-------------------	--------

Construction	Support and Strain Relief Grips, Various Types of Pulling	Application Sector	Industrial
--------------	-----------------------------------------------------------	--------------------	------------

Standard	UL/CSA Approval (consult factory)
----------	-----------------------------------

Technical Information

Maximum Cable Range	3 in	Minimum Cable Range	3.49 in
---------------------	------	---------------------	---------

Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
----------	-------------------------------	----------	--------------------------------------------------

Load	Approx. Break Strength: 16200
------	-------------------------------