



Pass and Seymour Manual Controller

Part No. PS20AC2HP



Double-Pole, Single Phase Switch, Back and Side-Wire, HP Rated.
20A, 277V.

Features & Benefits

High horsepower rating, up to 3HP for heavy-duty applications. Compact design provides ease of installation. Box lug terminals. Single piece moveable and stationary contact arms with oversized silver cadmium buttons provides excellent continuity and long life. Made in USA. Wire pockets and thick wall arc barriers. Cold-rolled steel NEMA 3R enclosure with polyester urethane finish conforms to OSHA lockout requirements. Type 3R enclosure has 2-1/2 inch, 3/4 inch, and 1 inch concentric knockouts on bottom. Accepts #4 AWG. cULus listed.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	Mexico	Application Sector	Industrial
Standard	UL 20		

Dimensions

Product Width US	1.32 in	Product Depth US	1.073 in
Product Height US	3.281 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Contact Rating	20Amp, 120/277Vac	Closed Contact Resistance	Toggle
Amperage	20 A	Number of Poles	Double Pole
Wattage	2 W	Voltage	120.0 V
