



400A 600V, Cable Size 2/0 - 4/0, Female Cam-Type Plug, Yellow

## Features & Benefits

- Thermoplastic elastomer housing for outstanding impact and chemical resistance
- Exceptional seal for maintaining NEMA Type 3R and 4 integrity
- Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product
- Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity
- Heavy-duty hex set screws allow greater termination torque
- Copper wire provides quality strain relief
- Copper shim bundles wire strands to reduce "splaying."

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Application Sector	Commercial/Industrial
Standard	UL, cCSAus		

### Dimensions

Product Length US	6.8 in
-------------------	--------

### Technical Information

Amperage	400 A	Number of Poles	Single Pole
Wire Size	2/0 - 4/0	Voltage	600.0 V

---

Environmental Conditions

Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4

---