




Pass and Seymour  
60A 4 Pole 5 Wire Fusible Mechanical Interlock  
Part No. PS560FMIR7W

4-Pole, 5-Wire, Fusible Mechanical Receptacle. 6 amp, 277/480V.



## Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

## Specifications

### General Info

|                   |                |                    |            |
|-------------------|----------------|--------------------|------------|
| Product Line      | Pass & Seymour | Color              | Gray       |
| Country Of Origin | United States  | Application Sector | Industrial |
| Standard          | UL Listed      |                    |            |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 9.13 in | Product Depth US | 9.94 in |
| Product Height US | 24.5 in |                  |         |

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

### Technical Information

---

|          |         |                 |       |
|----------|---------|-----------------|-------|
| Phase    | Three   | Number of Wires | 5     |
| Amperage | 60 A    | Number of Poles | 4-Way |
| Voltage  | 277.0 V |                 |       |

---