



On-Q  
12VDC 30W Power Supply  
Part No. PW7725

Powers connected home devices by converting high voltage alternating current (AC) to low voltage direct current (DC)



## Features & Benefits

Package includes a DC power supply with 2 ft barrel connector plug and a 1.5 ft AC power plug IEC C13/C14 connections  
Stacks neatly in enclosure with AC1031 power strip

## Specifications

### General Info

Product Line	On-Q	UPC Number	804428028475
Country Of Origin	China	Application Sector	Residential
Standard	UL, cULus, CE, FCC, C-Tick, RoHS		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

### Additional Information

RoHS Conformant	Yes
-----------------	-----

### Technical Information

Output Voltage	12 V	Connection	DC Barrel
Amperage	2.5 A	Input Voltage	100 to 240 V

---

Environmental Conditions 10 to 90% (relative humidity, non-condensing)

---