



radiant Collection  
radiant® LED/CFL Dimmer, White  
Part No. RHL743PW



Upgrade your space with precise dimming control and exceptional style. This dimmer from the radiant® Collection is optimized for use with LED bulbs and fixtures compliant with the SSL 7A standard for energy efficiency. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

SSL 7A - Compliant, this dimmer is for use with LED bulbs and fixtures also designed to the SSL 7A standard for efficiency. For use in both single-pole and 3-way applications.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

No derating\* required for 2-gang applications. \* Reducing the maximum wattage a dimmer can handle. This is sometimes required for multi-gang applications.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Constant memory features returns lights to their previous level after a power failure or outage.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

|                    |                           |                         |                              |
|--------------------|---------------------------|-------------------------|------------------------------|
| Product Line       | Pass & Seymour            | Replaced by Part Number |                              |
| Color              | White                     | Finish                  | Matte                        |
| Country Of Origin  | China                     | Features                | Locator Light                |
| Switch Type        | Paddle, Slider            | Number of Switches      | 1                            |
| Application Sector | Residential               | Standard                | CSA Listed, cULus, UL Listed |
| Warranty Type      | Limited Lifetime Warranty | Type                    | Dimmer                       |

---

## Dimensions

---

|                   |         |                  |        |
|-------------------|---------|------------------|--------|
| Product Width US  | 1.29 in | Product Depth US | 1.0 in |
| Product Height US | 3.18 in |                  |        |

---

## Listing Agencies / 3rd Party Agencies

---

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

---

## Technical Information

---

|                          |  |                 |                        |
|--------------------------|--|-----------------|------------------------|
| Frequency Rating         | 120VAC 60 Hz                           | Connection      | Screw Terminals        |
| Number of Gangs          | 1                                      | Amperage        | 5.5 A                  |
| Bulb Compatibility       | CFL, Halogen, Incandescent, LED        | Number of Poles | 3-Way, Single Pole     |
| Wattage                  | 700 W                                  | Mounting Type   | Box                    |
| Voltage                  | 120.0 V                                | Load            | LED, CFL, Incandescent |
| Environmental Conditions | Humidity: Less than 95% non condensing |                 |                        |

---