




radiant Collection
radiant® 4-Button Digital Timer, White
Part No. RT2W



Installs easily in place of a standard light or fan switch, or older spring-wound timer and includes manual on/off through the paddle switch for added convenience. A locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Works with a variety of light bulbs or fixtures, including: Incandescent, LED, fluorescent, compact fluorescent (CFL), magnetic low-voltage (MLV) and electronic low-voltage (ELV), 1/6 hp.

Automates control of lights for energy and cost savings. Also includes manual on/off through the paddle switch for added convenience.

Lets you select a desired preset shut-off time, including 60, 40, 20 and 10 minutes.

Installs easily in place of a standard light or fan switch, or older spring-wound timer.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

More color options available to fit any style.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------------|------------------------|
| Product Line | Pass & Seymour | Replaced by Part Number | |
| Color | White | Country Of Origin | China |
| Features | Timer | Switch Type | Paddle |
| Number of Switches | 1 | Application Sector | Residential/Commercial |
| Standard | cULus | Warranty Type | 5-Year |
| Type | Switch | | |

Dimensions

| | | | |
|------------------|---------|------------------|---------|
| Product Width US | 1.69 in | Product Depth US | 1.88 in |
|------------------|---------|------------------|---------|

| | |
|-------------------|----------|
| Product Height US | 3.281 in |
|-------------------|----------|

Technical Information

| | | | |
|------------|--------------------|--------------|-------|
| Connection | Back and side wire | Coil Voltage | 120 V |
|------------|--------------------|--------------|-------|

| | | | |
|----------------|----------|-----------------|---|
| Contact Rating | 600Watts | Number of Gangs | 1 |
|----------------|----------|-----------------|---|

| | | | |
|-------------------|---|----------|------|
| Number of Buttons | 4 | Amperage | 15 A |
|-------------------|---|----------|------|

| | | | |
|--------|-------------|-----------------|-------------|
| Action | Single Pole | Number of Poles | Single Pole |
|--------|-------------|-----------------|-------------|

| | | | |
|----------------|--------|--------------|---------------|
| Indoor/Outdoor | Indoor | Timing Range | 10-60 minutes |
|----------------|--------|--------------|---------------|

| | | | |
|---------|-------|---------------|-----|
| Wattage | 600 W | Mounting Type | Box |
|---------|-------|---------------|-----|

| | |
|---------|---------|
| Voltage | 120.0 V |
|---------|---------|
