



**Wiremold**  
**Plug-In Outlet Center Unit / 120V/15A/10 O/L /lighted switch/6' cord**  
Part No. UL210BC



Ten outlets, rugged gray aluminum housing, 15A, lighted switch. 6' (1.8m) 14/3 SJT black cord with NEMA5-15 plug. Length 13" (330mm), width 3 1/2" (89mm). Receptacle center-to-center 1 15/16" (49mm). Snap-on, slide-off mounting.

## Features & Benefits

Ten outlets, rugged gray aluminum housing, 15A, lighted switch. 6' (1.8m) 14/3 SJT black cord with NEMA5-15 plug. Length 13" (330mm), width 3 1/2" (89mm). Receptacle center-to-center 1 15/16" (49mm). Snap-on, slide-off mounting.

## Specifications

### General Info

|                       |   |                    |              |
|-----------------------|---|--------------------|--------------|
| Product Line          | Wiremold  | UPC Number         | 786776100860 |
| Country Of Origin     | Mexico  | Receptacle Type    | Simplex      |
| Number of Receptacles | 10  | Application Sector | Commercial   |
| Standard              | cULus Recognized: File E66421 Guide<br>XBYS XUHT VZCA | Type               | PIOC         |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 3.5 in  | Product Depth US | 3.58 in |
| Product Length US | 13.0 in |                  |         |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | E66421 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

### Buy American Act Compliance

---

|       |     |
|-------|-----|
| NAFTA | Yes |
|-------|-----|

---

#### Additional Information

---

|                 |     |
|-----------------|-----|
| RoHS Conformant | Yes |
|-----------------|-----|

---

#### Technical Information

---

|       |        |                  |       |
|-------|--------|------------------|-------|
| Phase | Single | Frequency Rating | 60 Hz |
|-------|--------|------------------|-------|

---

|          |      |                |          |
|----------|------|----------------|----------|
| Amperage | 15 A | Enclosure Type | Aluminum |
|----------|------|----------------|----------|

---

|               |                    |         |         |
|---------------|--------------------|---------|---------|
| Mounting Type | Snap-on, Slide-off | Voltage | 125.0 V |
|---------------|--------------------|---------|---------|

---

|                          |                        |
|--------------------------|------------------------|
| Environmental Conditions | Dry interior locations |
|--------------------------|------------------------|

---