



The Cat 6 RJ45 Keystone Coupler couples two high-speed network cables. The female to female coupler meets the EIA/TIA 568A Category 6 specifications.

## Features & Benefits

|                                    |   |
|------------------------------------|---|
| RJ45 Cat 6 Coupler Keystone Insert | Supports up to 10 gigabit Ethernet connection                       |
| No tools required                  | Exceeds Category 6 component standard: Ensures standards compliance |

## Specifications

### General Info

|                    |                           |                  |  |
|--------------------|---------------------------|------------------|--|
| Product Line       | On-Q                      | Color            | White  |
| Finish             | Matte                     | UPC Number       | 804428065968   |
| Country Of Origin  | Taiwan, Province Of China | Package Quantity | 1  |
| Application Sector | Residential               | Standard         | CSA, cULus, RoHS, ANSI/UL 1863, Flame-Retardant Plastic UL 94V-0 |
| Type               | Coupler                   |                  |  |

### Technical Information

|                             |              |                       |           |
|-----------------------------|--------------|-----------------------|-----------|
| Category Performance Rating | Cat 6        | Termination Style     | Coupler   |
| Gauge                       | 22 to 24 AWG | Cable Type            | Cat 6     |
| Amperage                    | 1.5 A        | Operating Temperature | 14°-140°F |

---

Environmental Conditions

0 to 93% (relative humidity, non-condensing)

---