



1.6 AMP Wide Slide Dehummer Fan Control

## Features & Benefits

- 4 Speed fan control with easy : slide to off" operation
- De-hummer feature virtually eliminates fan motor : hum" for quiet fan speed control
- Constant memory returns lights to previous level after a power failure
- 1.6A Rating single pole operation
- Supports other colors with WSKIT\*\* interchangeable face plates

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	China	Application Sector	Residential
Standard	CSA Listed, cULus, UL Listed		

### Dimensions

Product Width US	1.75 in	Product Depth US	1.25 in
Product Height US	4.25 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

---

---

Connection	Back Wired	Contact Rating	120VAC
Amperage	1.6 A	Number of Poles	Single Pole
Speed Range	Variable	Voltage	120.0 V
Environmental Conditions	Indoor Only		

---