



Wiremold  
Exterior Box Cover Assembly, 2 NEMA 5-20R Locking Duplex Receptacles, Gray (COVER ONLY)  
Part No. XB814C520GY



The gray Outdoor Ground Box cover assembly is prewired on a single circuit with (2) 20A weather resistant duplex receptacles. **CAUTION:** All ground box electrical circuits must be protected by a Ground Fault Circuit Interrupter upstream from the ground box. **NOTE:** Cover must be closed while in use. Use only molded plug and cord assemblies that are rated for outdoor use. **NOTE:** Maximum length of plug allowed at end of cord is 3" (76mm).

## Features & Benefits

cUL Coming Soon	UL listed to UL50E Type 6P (NEMA 6P) and IP68 requirements while in use
ADA compliant	Outdoor-rated construction
Keeps receptacles and connections dry even when submerged	

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776187212
Country Of Origin	China	Construction	Assembled
Number of Knockouts	1	Application Sector	Commercial
Standard	UL Listed Outdoor In-Ground Boxes: File E486738 Guide QCNL.	Type	Cover

### Dimensions

Product Width US	7.375 in	Product Height US	19.625 in
Product Length US	14.0 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E486738	cULus Listed	Yes
---------------------	---------	--------------	-----

### Additional Information

RoHS Conformant	Yes	Product Environmental Profile	Yes
-----------------	-----	-------------------------------	-----

### Technical Information

Number of Outlets	4
-------------------	---