Pass and Seymour
Heavy Duty Momentary Toggle Switch, Ivory
Part No. 1250-I



Single-Pole, Double-Throw Switch. 15A, 120/277VAC rating.Tested to 3 Amps, 24Vdc rating.

Features & Benefits

Oversize silver alloy contacts for long life and better heat dissipation.

Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.

Fiber terminal insulation barriers standard.

Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.

Bodies, covers, and toggles molded of durable nylon.

Single Pole-Double Throw and Double Pole-Double Throw.

Locking Switches supplied with one 1498-NT key.

Normally open.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Specifications

General Info

Product Line	Wattstopper	Color	Ivory
UPC Number	754182928149	Country Of Origin	China

Dimensions

Product Width US	2.0 in	Product Weight US	0.15 lb
Product Volume US	28.12 cu in	Product Depth US	4.5 in
Product Height US	2.5 in		

Technical Information

Amperage	15 A