



Tamper-Resistant Display Receptacle, 15A 125V With Brass Plate and plug.

Features & Benefits

- Dual mechanical shutter system to help prevent insertions of foreign objects
- Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly
- Easily accessed break-off line contact connecting tab for fast and easy split circuit wiring
- .032 inch thick brass triple-wipe power contacts for lasting retention
- Auto-ground clip assures positive ground

Specifications

General Info

Product Line	Pass & Seymour	Color	Brass
Finish	Metallic	UPC Number	785007108767
Country Of Origin	United States	Receptacle Type	5-15R
Number of Receptacles	1	Features	Recessed
Outlet Type	Commercial	Application Sector	Commercial
Standard	cULus, FEDSPEC	Type	Outlet

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Seismic Tested	No	Is Tamper-Resistant	Yes
----------------	----	---------------------	-----

Amperage	15 A	Is Weather Resistant	No
----------	------	----------------------	----

Indoor/Outdoor	Indoor	Connection Type	Wired
----------------	--------	-----------------	-------

Environmental Conditions	85% (relative humidity, non-condensing)
--------------------------	---
