
radiant Collection

# Discontinued - radiant® 15A Hospital Grade Tamper Resistant Self Test GFCI USB Type A/C Outlet, Ivory

Part No. 1597HGTRUSBACI



## Features & Benefits

First outlet of its kind to add USB connection to a GFCI outlet for easier charging, anywhere

Rated for use in hospitals and healthcare facilities, this outlet offers superior durability and reliable ground fault protection. Includes a trip indicator light and reset button on the outlet for easy, accessible troubleshooting

Includes traditional power outlets, as well as one USB Type-A and one USB Type-C port for convenient charging. Shares 2.0A charging capacity between both ports

Self-tests every three seconds, ensuring continuous ground fault protection for greater safety. Additionally, in case of test failure, the indicator light (red LED) will flash to signal there is an issue and the outlet should be replaced

Equipped with proven SafeLock™ feature which disconnects power to the outlet if any critical components are damaged for added protection

Prevents the insertion of foreign objects while maintaining a discreet, invisible effect with patented, black "invisi-shutter" system. Meets NEC® Tamper-Resistant requirements

Installs quickly thanks to a redesigned side wire cavity for easier access

Can provide ground fault protection to downstream outlets through feed-thru wiring

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Pass & Seymour | Color | Ivory |
| Finish | Matte | Country Of Origin | China |
| Number of Receptacles | 2 | Features | USB-A Charging, USB-C Charging |
| Outlet Type | GFCI, Indoor, Residential, Self-Test, Tamper-Resistant, USB-Charging | Application Sector | Residential/Commercial |
| Warranty Type | 1-Year Limited Warranty | Type | Duplex, GFCI, Tamper-Resistant, USB |

### Listing Agencies / 3rd Party Agencies

| | | | |
|---|---|---|---|
| CSA Listed | Yes | cULus ListingNumber | E140596 |
| cULus Listed | Yes | CSA File Number | CSA C22.2 No. 223, CSA C22.2 No. 42 |

### Additional Information

| | |
|---|---|
| RoHS Conformant | Yes |

### Technical Information

| | | | |
|---|---|---|---|
| Is Tamper-Resistant | Yes | USB Amperage | 2.1 A |
| Number of USBs | 2 | Number of Gangs | 1 |
| Amperage | 15 A | Is Weather Resistant | No |
| Indoor/Outdoor | Indoor | Wattage | 1875 W |
| Mounting Type | Box | Voltage | 125 V |