Ortronics
Swing-EZ Wall Rack - Heavy Duty - Black - 25.00 in D
Part No. 19-21-T25DHYDTB



19.75''W x 24.25''H x 25.00''D

Features & Benefits

Swing-EZ Wall Racks offer flexibility: The 25" deep unit gives the flexibility of mounting equipment where space is a premium and a full size rack cannot be used for small offices.

12-24 threaded EIA hole pattern: Standards compliant to mount numerous types of 19" panels and equipment.

Reinforcement pan attached to bottom of Swing-EZ: Sturdy and holds equipment up to 150lbs.

Self squaring assembly: No additional tools required

Front swing gate with latch pins and bolts on both: Allows you to open swing gate either left or right and easy access to rear of panels and equipment.

Side panels fold flat for shipping: Unfold for easy on site assembly.

Base includes 3" feed through holes: Allows cable delivery from bottom of rack.

•Includes 12-24 mounting screws: Do not have to purchase as separate item

Specifications

General Info

Product Line	Ortronics	Color	Black
UPC Number	662875580898	Country Of Origin	United States
Application Sector	Commercial	Type	Rack

Dimensions

Product Width US	19.75 in	Product Depth US	25.0 in
Product Height US	21.0 in		

Additional Information

RoHS Conformant	Yes	Product Environmental Profile	Yes