



15A/125A Trademaster® Self-Grounding, Tamper-Resistant Duplex Receptacle

Features & Benefits

Quality Materials, durability, and time-tested design

Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007240016
Country Of Origin	China	Number of Receptacles	2
Outlet Type	Self-Grounding, Tamper-Resistant	Application Sector	Commercial, Residential
Standard	cULus UL498, CSA C22.2 No. 42	Type	Outlet

Dimensions

Product Width US	1.32 in	Product Depth US	1.0 in
Product Height US	3.31 in		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Additional Information

Product Environmental Profile Yes

Technical Information

Is Tamper-Resistant Yes Temperature Rating -30° - 60° C

Amperage 15 A Number of Poles Double Pole

Wire Size 14 - 12 AWG Indoor/Outdoor Indoor
