Pass and Seymour

30A 125/250V 10-30R Straight Blade Single Surface Receptacle, 3-Pole, 3-Wire

Part No. 388



Straight Blade Receptacle 30A 125/250V 3-Pole 3-Wire

Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	China	Standard	UL 498

Dimensions

Product Width US	2.8 in	Product Depth US	2.41 in
Product Height US	5.65 in		

Technical Information

Connection	Non Ground	Number of Wires	3
Amperage	30 A	Number of Poles	Double Pole
Wire Size	4	Voltage	125 V