



Quiktron  
Q-Series Patch Cords, CAT5E, Non-Booted, Black, 20 FT  
Part No. 560-135-020



Q-Series patch cords are a perfect solution for when cost and speed of delivery are top priority. Designed to perform to TIA-568.2-D standards, Q-Series cords are available in a full range of colors and lengths, stocked and ready to order.

## Features & Benefits

Connector: 50micron gold plated RJ45 male to male

Conductor: 24AWG stranded copper

Warranty Type: Lifetime warranty

Price Sensitive: Perfect solution for when cost and speed of delivery are top priority

Standards Compliant: Perform to TIA-568.2-D standards

## Specifications

### General Info

|              |                   |                    |                        |
|--------------|-------------------|--------------------|------------------------|
| Product Line | Quiktron          | Color              | Black                  |
| UPC Number   | 884815750943      | Country Of Origin  | Vietnam                |
| Features     | Standard Diameter | Application Sector | Commercial, Industrial |
| Type         | Copper Patch Cord |                    |                        |

### Dimensions

|                   |        |                   |         |
|-------------------|--------|-------------------|---------|
| Product Weight US | 0.5 lb | Product Length US | 20.0 FT |
| Cable Length      | 20 ft  |                   |         |

### Additional Information

|                |     |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

### Technical Information

|                             |                           |                           |                |
|-----------------------------|---------------------------|---------------------------|----------------|
| Jacket Material             | PVC                       | Operating Temperature Min | -10 °C         |
| Category Performance Rating | Cat5e                     | Wire Gauge                | 24 AWG         |
| Storage Humidity            | 0-90% RH (Non-Condensing) | Plating Specification     | 50 μ in Gold   |
| Jacket Application          | Riser Rated               | Bend Radius               | 0.82 in        |
| Shielded/Unshielded         | Unshielded                | Termination Style         | Pre-Terminated |
| Conductor Stranding         | Stranded                  | Operating Temperature Max | 60 °C          |
| Jacket Rating               | CM Rated                  | Cable Diameter            | 0.205 in       |
| Braid                       | Non-braided Wiring        | Operating Temperature     | -10°-60°C      |
| Operating Humidity          | 0-90% RH (Non-Condensing) | Conductor Material        | Copper         |
| Voltage                     | 300.0 V                   | Storage Temperature       | -40° - 60° C   |