



**On-Q**  
**Cat 5e Patch Cable, 3 ft, White**  
Part No. AC3503WHV1



This component rated Cat 5e patch cable is constructed with a low profile, snagless boot that protects the tab from catching on other cables in a high density patch panel application.

## Features & Benefits

100 MHz patch cable supports 10 Gigabit Ethernet speeds

UL verified to support the Cat 5e performance patch cable specification

Snagless overmold prevents insertion tab from catching on other cables

24 AWG stranded patch cable :

## Specifications

### General Info

Product Line	On-Q	Color	White
UPC Number	804428031765	Country Of Origin	Taiwan, Province Of China
Application Sector	Residential	Standard	UL, CSA, FCC, 94V-0 Flame Retardant, RoHS

### Dimensions

Product Length US	3.0 FT
-------------------	--------

### Technical Information

Plug Type	RJ45 Plug	Attenuation	22 dB
Wire Size	24 AWG	Number of Conductors	4
Conductor Material	Copper		