




On-Q
Cat 5e Patch Cable, 25 ft, White
Part No. AC3525WHV1

This component rated Cat 5e patch cable is constructed with a low profile, snagless boot that protects the tab from catching on other cables in a high density patch panel application.



Features & Benefits

- 100 MHz patch cable supports 10 Gigabit Ethernet speeds
- UL verified to support the Cat 5e performance patch cable specification
- Snagless overmold prevents insertion tab from catching on other cables
- 24 AWG stranded patch cable :

Specifications

General Info

Product Line	On-Q	Color	White
UPC Number	804428031796	Country Of Origin	Taiwan, Province Of China
Application Sector	Residential	Standard	UL, CSA, FCC, 94V-0 Flame Retardant, RoHS

Dimensions

Product Length US	25.0 FT
-------------------	---------

Technical Information

Plug Type	RJ45 Plug	Attenuation	22 dB
Wire Size	24 AWG	Number of Conductors	4
Conductor Material	Copper		