



On-Q  
Cat 6 Patch Cable, 14 ft, Blue  
Part No. AC3614BEV1



This component rated Cat 6 patch cable is constructed with a low profile, snagless boot that protects the tab from catching on other cables in a high density patch panel application. These patch cables are 100% tested and

## Features & Benefits

250 MHz patch cable fully supports 10 Gigabit Ethernet speeds

UL verified to support the Cat 6 performance patch cable specification.

Snagless overmold prevents insertion tab from catching on other cables.

Patch cable exceeds 750 insertion cycles as specified in FCC part 68 Subpart.

## Specifications

### General Info

|                    |              |                   |  |
|--------------------|--------------|-------------------|--|
| Product Line       | On-Q         | Color             | Blue   |
| UPC Number         | 804428066842 | Country Of Origin | China  |
| Application Sector | Residential  | Standard          | UL, CSA, FCC, TIA/EIA-568-B2-1 meets or exceeds Cat 6 standards, 94V-0 Flame Retardant, RoHS |

### Dimensions

|                   |         |
|-------------------|---------|
| Product Length US | 14.0 FT |
|-------------------|---------|

### Technical Information

|                 |      |                |         |
|-----------------|------|----------------|---------|
| Jacket Material | PVC  | Wire Gauge     | 24 AWG  |
| Cable Type      | Cat6 | Cable Diameter | 0.25 in |