



On-Q
Cat 6 Patch Cable, 25 ft, Blue
Part No. AC3625BEV1



This component rated Cat 6 patch cable is constructed with a Low profile snagless boot that protects the tab from catching on other cables in highdensity patch panel application. These patch cables are 100% tested and exceed the patch cable standards

Features & Benefits

250 MHz patch cable fully supports 10 Gigabit Ethernet speeds

UL verified to support the Cat 6 performance patch cable specification.

Snagless overmold prevents insertion tab from catching on other cables.

Patch cable exceeds 750 insertion cycles as specified in FCC part 68 Subpart.:

Specifications

General Info

Product Line	On-Q	Color	Blue
UPC Number	804428066859	Country Of Origin	China
Application Sector	Residential	Standard	UL, CSA, FCC, TIA/EIA-568-B2-1 meets or exceeds Cat 6 standards, 94V-0 Flame Retardant, RoHS

Dimensions

Product Length US	25.0 FT
-------------------	---------

Technical Information

Jacket Material	PVC	Wire Gauge	24 AWG
Cable Type	Cat6	Cable Diameter	0.25 in