



On-Q
Active Premium High Speed HDMI™ Cable with Ethernet (15m) 18 Gbps
Part No. ACAA15BK



The 18Gbps Active Copper HDMI Cable, 15m, supports 18.2Gbps bandwidth, UltraHD 4K@60Hz 4:4:4, HDR, Deep Color, ARC, and Ethernet. It meets the CSA FT4 Vertical Flame Test with a max char height of 59 inches, more stringent than the UL1685 test. Enhanced retention clips require 4.5 lbs of pull-force to remove. The directional cable features color-coded ends to easily discern the Display end from the Source end and is solely powered by the source device, requiring no external power adapter. Rated CMG/CL3, it is ideal for projector-based home theaters or any residential installation requiring a longer run.

Features & Benefits

Supports 18.2 Gbps bandwidth, UltraHD - 4K@60Hz 4:4:4, High Dynamic Range (HDR), Deep Color, ARC, Ethernet

Meets CSA FT4 Vertical Flame Test - This testing procedure has cables mounted on a vertical tray, which are then exposed for 20 minutes to a 70,000 BTU/hour flame

The FT4 max char height of 59 inches is more stringent than the UL1685 vertical tray flame test max char height of 78 inches

Enhanced retention clips keep the cable firmly in place, requiring 4.5 lbs of pull-force to remove

Directional cable features color-coded cable ends to easily discern Display end from the Source end

Solely powered by the source device - do not require external power adapter

Rated: CMG / CL3

Ideal applications: Projector-based home theater or any residential installation where a longer run is required

Available in lengths from 10 to 15 meters

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Specifications

General Info

Product Line	On-Q	Color	Black
--------------	------	-------	-------

UPC Number	804428432807	Country Of Origin	China
------------	--------------	-------------------	-------

Dimensions

Product Length US	49.2 FT
-------------------	---------

Technical Information

Connector	HDMI Type A male to Type A male, 24K Gold-plated	Number of Pins	19
-----------	--	----------------	----

Data Transfer Rate	18.2 Gbps
--------------------	-----------
