Pass and Seymour

Nylon Cord Grip, 1/2-in NPT Straight, .312-.375 OD Range

Part No. CGN50312



Non-Metallic Cord Connectors are constructed of a durable, nylon material which offers excellent corrosion resistance, is lightweight, durable and ideal for use in damp environments. Nylon Cord Connectors are ideally suited for use in applications with moisture or washdowns and they provide an environmental seal against dirt, coolants, as well as other chemicals.

Features & Benefits

- Heavy duty Nylon body is resistant to impact and corrosion
- Available in straight, 90: , and underground feed styles
- Rugged construction suitable for various industrial applications such as MRO, food processing, water/waste water, marine, pulp & paper, and petrochemical
- Rubber grommet provides a liquid-tight seal and reduces cord pull-out while resisting chemicals
- Color coded grommets make for easy identification and ease of installation

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	India
Construction	Nylon Cord Grip	Application Sector	Commercial/Industrial
Standard	UL Listed		

Dimensions

Product Width US	0.375 in	Product Length US	0.5 in

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes

Technical Information

Maximum Cable Range	0.312 in	Minimum Cable Range	0.375 in